

ANDERSON NEGELE PRESSURE SENSOR DAN-HH

DAN-HH

DAN-HH

- Pressure measurement in pipes and containers
- High temperatures up to 150 ° C
- Front-flush, hygienic and easily sterilizable installation with EMZ-352 or EHG -... / 1 "connection
- Complies with 3-A Sanitary Standard 74-06, Third Party Verified (Only with Tri-Clamp Mount)
- EHEDG-certified hygienic CLEANadapt process connection



PRODUCT DESCRIPTION

We market high quality printing and design from our supplier Anderson-Negele, which meets the highest standards of process engineering, and is the perfect solution for applications for food, pharmaceuticals, breweries, cosmetics and pharmaceutical processes.

The products of Anderson-Negele are manufactured according to the concept "Hygienic by Design", which is reflected in the special process adapters: CLEANadapt and PHARMadapt as well as the unique design of the instruments.

Pressure sensor, type DAN-HH -...

This unit uses a built-in piezoelectric converter to convert the process value into a corresponding mV signal. The mV signal then passes through a customer-specific linearization and signal processing. The resulting signal corresponds to industry standard 4 ... 20 mA. This mA signal is factory-set for this unit's measurement range. For relative pressure sensors, the back of the membrane is ventilated; that is, this sensor measures the mean pressure and / or vacuum relative to air pressure.

For an absolute pressure sensor, the measured value is relative to a perfect theoretical vacuum. This means that the signal changes with the air pressure for the respective environment.

Other features:

- CIP / SIP cleaning up to 150 ° C
- Product-related materials are FDA-compatible
- Stainless steel sensor and product-related materials
- Additional process connections in combination with CLEANadapt: Flange (DIN 11851), VARIVENT, m.f.

Please contact us for more information and price.

Please refer to the image below for ordering information.

Order code	
DAN-HH	Compact pressure sensor
	Process Connection
	TC1,5 (Tri-Clamp 1,5"; incl. 3-A TPV verification)
	TC2 (Tri-Clamp 2"; incl. 3-A TPV verification)
	S (CLEANadapt G1"; without 3-A TPV verification)
	Measurement range absolute
	2ABS (absolute pressure cell 0...2 bar)
	3ABS (absolute pressure cell 0...3 bar)
	7ABS (absolute pressure cell 0...7 bar)
	14ABS (absolute pressure cell 0...14 bar)
	20ABS (absolute pressure cell 0...20 bar)
	[end value] ABS other absolute pressure range, specify required range in "bar" with "ABS"
	Measurement range relative
	1REL (relative pressure cell 0...1 bar)
	2REL (relative pressure cell 0...2 bar)
	3REL (relative pressure cell 0...3 bar)
	7REL (relative pressure cell 0...7 bar)
	14REL (relative pressure cell 0...14 bar)
	20REL (relative pressure cell 0...20 bar)
	34REL (relative pressure cell 0...34 bar)
	-1...1REL (relative pressure cell -1...1 bar)
	-1...2,5REL (relative pressure cell -1...2,5 bar)
	-1...6REL (relative pressure cell -1...6 bar)
	-1...13REL (relative pressure cell -1...13 bar)
	[end value] REL other relative pressure range, specify required range in "bar" with "REL"
	Electrical connection
	M12 (M12-Stecker 1.4305)
DAN-HH /	S /
	14ABS /
	M12

;

SPECIFICATIONS

Approvals	3-A, FDA
IP Class	IP69K
Measuring Range	0 ... 34 bar rel., -1 ... 13 bar rel. / 0 ... 20 bar abs.
Supply Voltage DC Max	36
Supply Voltage DC Min	12
Surface Finish	0.6
Temperature ambient from	-20
Temperature ambient to	50
Temperature range of media from	0
Temperature range of media to	150